


LEPTON SERIES

Single element MWIR detectors with different geometries, packaging solutions and preamplifier boards


Uncooled, high-speed operation at room temperature
(1- / 2- / 3-TEC cooled options also available)



LEPTON DETECTOR
Uncooled, TO-5 / SMD packages



LEPTON DETECTOR
n-TEC cooled, TO-8 package




LEPTON ANALOG PREAMPLIFIER




LEPTON PREAMPLIFIER
WITH USB OUTPUT


- ▶ Detector geometries: 1x1 mm², 2x2 mm²
(ask us for custom designs or other geometries)
- ▶ Spectral response: 1 - 5 microns (peak response @ 3.7 microns)
- ▶ D*(λ_{peak}) (typ): 2x10⁹ Jones
- ▶ Biasing voltage (typ): 10 V
- ▶ Pixel resistance (typ): 0.8 - 1.0 MΩ
- ▶ Responsivity (@V_b=10 V):
 - ▶ 1x1 mm²: 9x10³ V/W
 - ▶ 2x2 mm²: 4.5x10³ V/W
- ▶ Packaging options:
 - ▶ Uncooled: SMD (non-hermetic) / TO-5 (hermetic)
 - ▶ n-TEC cooled: TO-8 (hermetic)
- ▶ Operating temperature:
 - ▶ SMD package (non-hermetic): 5 °C - 70 °C
 - ▶ TO-5 & TO-8 (hermetic): -40 °C - 85 °C
- ▶ Response time (room temperature) (typ): < 2 us
- ▶ Readout electronics: not included (see preamp modules)
- ▶ Device dimensions and footprint:
 - ▶ SMD packaging: 10 mm x10 mm, 2 connections (replicated on each side), with sapphire window (AR)



- ▶ TO-5 hermetic packaging: 9.14 mm (0.360") diameter, 4 connections (only 2 in use), separation between leads 5.84 mm (0.230"), cap with sapphire window (AR)



- ▶ TO-8 hermetic packaging: 15.24 mm (0.600") diameter, 12 connections (1-TEC, only 6 in use) / 16 connections (2- / 3-TEC, only 6 in use), separation between leads 10.16 mm (0.400"), cap with sapphire window (AR)



1-TEC

2- / 3-TEC


LEPTON PREAMPLIFIER MODULES

LEPTON ANALOG PREAMP

Parameter	Value	Unit
Channels	1	
Detector included	LEPTON SERIES 1x1 mm ² or 2x2 mm ²	
Band of IR detection	1.0 - 5.0 microns (MWIR)	
Sensor biasing V_b	Rotary switch, selectable, 4 values	
Values	1.25, 2.50, 5.00, 10.00	V
Gain G	Rotary switch, selectable, 4 values	
Values	10^4 , 10^5 , 10^6 , 10^7	V/A
Analog bandwidth	Gain dependant (see chart below)	kHz
R_{Dark} cancellation	Cermet trimmer (11 turns)	
Min. value	10	k Ω
Max. value	1.01	M Ω
Output	Analog voltage	
Coupling	DC, BNC connector	
Range	± 10	V
Current	± 10	mA
Noise	5 pA @ 1,000 Hz and max. gain	
Power supply	5 (min. 4.5, max. 5.5)	V
Max. current	60	mA
Connector	USB mini B	
Isolation voltage	1,000	VDC
Dimensions (L x W x H)	75.80 x 35.10 x 28.70	mm

LEPTON PREAMP WITH USB OUTPUT

Parameter	Value	Unit
Channels	1	
Detector included	LEPTON SERIES 1x1 mm ² or 2x2 mm ²	
Band of IR detection	1.0 - 5.0 microns (MWIR)	
Sensor biasing V_b	Digitally selectable, 4 values	
V_b 1	1.25	V
V_b 2	2.5	V
V_b 3	5	V
V_b 4	10	V
Gain G	Digitally selectable, 4 values	
Values	10^4 , 10^5 , 10^6 , 10^7	V/A
Analog bandwidth	Gain dependant (see chart below)	kHz
R_{Dark} cancellation	Cermet trimmer (11 turns)	
Min. value	10	k Ω
Max. value	1.01	M Ω
Digital output	USB 2.0 mini B connection	
ADC resolution	14 bits	
Sampling rate	20k samples per second (max)	
Analog output	Preamplifier stage	
Coupling	DC	
Connector	SMB or BNC	
Range	± 10	V
Current	± 10	mA
Noise	5 pA @ 1,000 Hz and max. gain	
Power supply	5 (min. 4.5, max. 5.5)	V
Max. current	100	mA
Connector	USB mini B	
Isolation voltage	1,000	VDC
Operation Software	LEPTON DIGITAL AMPLIFIER SW (provided)	
Dimensions (L x W x H)	89.30 x 35.10 x 26.30	mm



iSweek www.isweek.cn

公司名: 深圳市工采网络科技有限公司

电话: + 86-755-83289036

地址: 广东省深圳市南山区高新南一道中国科技开发院3号楼16层

传真: + 86-755-83289052

邮箱: sales@isweek.cn